



## Combination spanner, phosphated, Width across flats: 4,5mm



### Order data

Order number	613900 4,5
GTIN	4045197441546
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw width.  
With oval shaft.

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome vanadium steel, phosphated.

### Technical description

Width across flats	4.5 mm
maximum jaw height h <sub>1</sub>	4 mm
Spanner length L	100 mm
Width across flats	metric
maximum ring height h <sub>2max</sub>	6 mm
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

