

**Pracklinghaus****Long-bladed hand-operated shears, Model: 4/300****Order data**

Order number	769936 4/300
GTIN	2050001931757
Item class	76L

**Description****Version:**

Sturdy shears body of quenched and tempered steel. Moving blade guides free of play (with low friction losses), blades of special tool steel, specially hardened and ground. Lever arm with counterweight spring for protection in the event of accidents, all pivot pins adjustable, all models with steplessly adjustable clamping arm.

With compound action, cuts sheet metals and round steel bar.

**Colour:**

Red-brown.

**Note:**

For spare upper blade No. 769938 and spare lower blade No. 769939 see the spare parts list.

For spare upper blade No. 769938 and spare lower blade No. 769939 see the spare parts list.

**Technical description**

Upper blade length	355 mm
Weight	30 kg
Cutting capacity sheet thickness	up to 4 mm
Cutting capacity round steel bar $\varnothing$	up to 13 mm

Lower blade length	300 mm
Model	4/300
Type of product	Cutting pliers

---

## Accessories

Blade(lower blade) suitable for model 4/300	769939 4/300
Blade(upper blade) suitable for model 4/300	769938 4/300