

**Combination spanner, phosphated, Width across flats: 24mm****Order data**

Order number	613900 24
GTIN	4045197385222
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, phosphated.

Technical description

Spanner length L	280 mm
maximum jaw height h1	12 mm
Width across flats	24 mm
Width across flats	metric
maximum ring height h_{2max}	16 mm
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

