

**Combination spanner, phosphated, Width across flats: 14mm****Order data**

| | |
|--------------|---------------|
| Order number | 613900 14 |
| GTIN | 4045197385147 |
| Item class | 62A |

Description**Version:**

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, phosphated.

Technical description

| | |
|--------------------------------|-----------------------|
| Width across flats | 14 mm |
| Spanner length L | 180 mm |
| maximum jaw height h1 | 6.5 mm |
| Width across flats | metric |
| maximum ring height h_{2max} | 12 mm |
| Ring setting | 15 degrees |
| Material | Chrome vanadium steel |
| Surface | phosphated |
| Product name attribute | phosphated |
| Type of product | Spanner |

