



JOKER 6001 Switch open ended spanner / ratchet ring spanner, reversible, 15° offset, Width across flats: 19mm



Order data

Order number	614875 19
GTIN	4013288184764
Item class	63F

Description

Version:

Die-forged. Ring end with smooth-running sturdy precision ring ratchet (80 teeth) with a particularly small working arc of 4.5°.

The open end has a bi-hexagon profile and a replaceable hardened metal plate, which fulfils a stop function, preventing slippage and allowing a small working arc.

Ring end 15° offset, reversible.

Material:

Chrome molybdenum steel, matt chrome-plated.

Technical description

Ring Ø D	34.7 mm
Ring thickness h ₂	11 mm
Width across flats	metric
Width across flats	19 mm
Spanner length L	246 mm
Jaw height h ₁	9.5 mm
Jaw width b	42 mm
Manufacturer's designation	6001 Joker Switch
Ring setting	15 degrees
Working arc	4.5 degrees

Material	Chrome molybdenum steel
Surface	matt chrome plated
Ratchet reversible	no
Type of product	Spanner

Accessories

Adapter for ratchet ring spanner Type 3	614850 3
---	----------