

Plug gauge H7, Nominal size Ø: 41 mm



Order data

Order number	484000 41
GTIN	2050001951519
Item class	48B

Description

Version:

The "Go" ends of these working gauges have a **wear allowance** to DIN 7164. Measuring body made of first class gauge steel, hardened, stress-relieved, ground, and lapped. Plug gauge with tolerance class H7.

Standard:

Toleranz und Abmaße nach **DIN EN ISO 1938-1, DIN 2245-1 und DIN 7164.**

Note:

- **Further intermediate sizes available on request or can simply be ordered at www.hoffmann-group.com, for instance No. 484000 size 82.**
- **For acceptance gauges (without wear allowance) see No. 484027.**
- **For gauges with intermediate sizes and all Ø with numeric tolerances see No. 484025.**

Technical description

Tolerance zone	H
Standard	DIN 7150-2
Standard	DIN 7164
Quality	7
Type of gauge	"Go" plug gauge
Type of gauge	"No Go" gauge
Type of gauge	"Go" plug gauge
Nominal size	41 mm
Calibration	M2

Type of product

Pug Gauge

ServicesCalibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm

028300 60

DAkkS calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm

028340 60