

## Plug gauge H7, Nominal size Ø: 62mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 484000 62     |
| GTIN         | 2050001951625 |
| Item class   | 48B           |

### Description

#### Version:

The "Go" ends of these working gauges have a **wear allowance** to DIN 7164. Measuring body made of first class gauge steel, hardened, stress-relieved, ground, and lapped. Plug gauge with tolerance class H7.

#### Standard:

Toleranz und Abmaße nach **DIN EN ISO 1938-1, DIN 2245-1 und DIN 7164.**

#### Note:

- **Further intermediate sizes available on request or can simply be ordered at [www.hoffmann-group.com](http://www.hoffmann-group.com), for instance No. 484000 size 82.**
- **For acceptance gauges (without wear allowance) see No. 484027.**
- **For gauges with intermediate sizes and all Ø with numeric tolerances see No. 484025.**

### Technical description

|                |                 |
|----------------|-----------------|
| Tolerance zone | H               |
| Standard       | DIN 7150-2      |
| Standard       | DIN 7164        |
| Quality        | 7               |
| Nominal size   | 62 mm           |
| Type of gauge  | "Go" plug gauge |
| Type of gauge  | "No Go" gauge   |
| Type of gauge  | "Go" plug gauge |
| Calibration    | M2              |

Type of product

Pug Gauge

**Services**DAkkS calibration "Go" / "No Go" plug gauge maximum  $\varnothing$  200 mm

028340 200

Calibration "Go" / "No Go" plug gauge maximum  $\varnothing$  200 mm

028300 200