

## Plug gauge H7, Nominal size Ø: 53mm



### Order data

Order number	484000 53
GTIN	2050001951557
Item class	48B

### Description

#### Version:

The "Go" ends of these working gauges have a **wear allowance** to DIN 7164. Measuring body made of first class gauge steel, hardened, stress-relieved, ground, and lapped. Plug gauge with tolerance class H7.

#### Standard:

Toleranz und Abmaße nach **DIN EN ISO 1938-1, DIN 2245-1 und DIN 7164.**

#### Note:

- **Further intermediate sizes available on request or can simply be ordered at [www.hoffmann-group.com](http://www.hoffmann-group.com), for instance No. 484000 size 82.**
- **For acceptance gauges (without wear allowance) see No. 484027.**
- **For gauges with intermediate sizes and all Ø with numeric tolerances see No. 484025.**

### Technical description

Tolerance zone	H
Standard	DIN 7150-2
Standard	DIN 7164
Quality	7
Type of gauge	"Go" plug gauge
Type of gauge	"No Go" gauge
Nominal size	53 mm
Calibration	M2
Type of product	Pug Gauge

---

**Services**DAkkS calibration "Go" / "No Go" plug gauge maximum  $\varnothing$  60 mm

028340 60

Calibration "Go" / "No Go" plug gauge maximum  $\varnothing$  60 mm

028300 60