

Plug gauge H7, Nominal size Ø: 64mm



Order data

| | |
|--------------|---------------|
| Order number | 484000 64 |
| GTIN | 2050001951717 |
| Item class | 48B |

Description

Version:

The "Go" ends of these working gauges have a **wear allowance** to DIN 7164. Measuring body made of first class gauge steel, hardened, stress-relieved, ground, and lapped. Plug gauge with tolerance class H7.

Standard:

Toleranz und Abmaße nach **DIN EN ISO 1938-1, DIN 2245-1 und DIN 7164.**

Note:

- **Further intermediate sizes available on request or can simply be ordered at www.hoffmann-group.com, for instance No. 484000 size 82.**
- **For acceptance gauges (without wear allowance) see No. 484027.**
- **For gauges with intermediate sizes and all Ø with numeric tolerances see No. 484025.**

Technical description

| | |
|-----------------|-----------------|
| Tolerance zone | H |
| Standard | DIN 7150-2 |
| Standard | DIN 7164 |
| Quality | 7 |
| Nominal size | 64 mm |
| Type of gauge | "Go" plug gauge |
| Type of gauge | "No Go" gauge |
| Calibration | M2 |
| Type of product | Pug Gauge |

Services

DAkkS calibration "Go" / "No Go" plug gauge maximum \varnothing 200 mm

028340 200

Calibration "Go" / "No Go" plug gauge maximum \varnothing 200 mm

028300 200