

## Setting ring DIN 2250 C, Nominal size $\varnothing$ : 59mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 484030 59     |
| GTIN         | 2050001955067 |
| Item class   | 48B           |

### Description

**Version:**

**Setting rings** (checking rings) of first class gauge steel, hardened, stress-relieved, ground and lapped. **Each setting ring is engraved with the actual size.** Manufacturer's tolerance for the bore is JS4.

**Application:**

For general applications, e.g. for setting and testing measuring tools.

**Standard:**

Nach **DIN 2250 C**.

**Note:**

**Other intermediate sizes up to 320 mm can be easily ordered, e.g. 484030 size 82.**

### Technical description

|                |             |
|----------------|-------------|
| Tolerance zone | JS          |
| Nominal size   | 59 mm       |
| Standard       | DIN 2250 C  |
| Material       | Gauge steel |

|                                     |              |
|-------------------------------------|--------------|
| Manufacturing tolerance of the bore | JS4          |
| Quality                             | 4            |
| Calibration                         | L7           |
| Type of product                     | setting ring |

**Services**

|  |            |
|--|------------|
| CalibrationSetting ring maximum Ø 100 mm       | 028400 100 |
| DAkkS calibrationSetting ring maximum Ø 200 mm | 028470 200 |