

LESSMANN®
THE GERMAN BRUSH COMPANY
**Cup brush Right-left knotted, stainless steel wire 0.50 mm, Brush Ø D1×
 thread M: 65XM14mm**

Order data

| | |
|--------------|---------------|
| Order number | 572205 65XM14 |
| GTIN | 4017359380130 |
| Item class | 57L |

Description
Version:

Smooth steel wire, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Right-left knotted for increased aggressiveness for heavy-duty brushing work. Very suitable for use at corners and edges, with a smooth action.

Application:

Specially to accept angle grinders.

With **M14 internal thread.**

Technical description

| | |
|--|-------------------------|
| Length of brush section H ₁ | 20 mm |
| Safety support ring | no |
| Bristle thickness | 0.5 mm |
| maximum speed | 12500 min ⁻¹ |
| Brush Ø D ₁ | 65 mm |

| | |
|------------------|----------------------|
| Thread M | M14 |
| Brush material | Stainless steel wire |
| Twisted knotting | Right-left knotted |
| Type of product | Cup brush |