

3M
Helmet combination PELTOR™ G3000 forest, Colour: ORANGE

Order data

Order number	097814 ORANGE
GTIN	4046719736218
Item class	04M

Description
Version:

The proven 3-piece head protection combination for forestry applications consisting of:

- **Safety helmet (G3000) with UV sensor and convenient ratchet system,**
- **Mesh visor of polyamide (5B)**
- **Shell-type ear defenders (SNR = 28dB H = 35dB, M = 26dB, L = 16dB).**

When the ear defenders are not in use they can easily be swung away upwards.

Application:

Forestry work all the year round, in particular using chainsaws.

Standard:

DIN 397 (Helm); DIN EN 352-3 (Gehörschutz); DIN EN 1731 (Visier)

Helmet characteristics: Safety characteristics down to -30 °C

Material of helmet shell: ABS

Width adjustment: Drejelukning

Size: 53 - 62 cm

Weight: 600 g

Technical description

Resistance to cold	up to -30 °C
--------------------	--------------

Width adjustment	Drejelukning
Weight	600 g
Size	53 - 62 cm
Helmet characteristics	Safety characteristics down to -30 °C
Material of helmet shell	ABS
Standard	DIN EN 352-3
Standard	DIN EN 1731
Standard	DIN EN 397
Type of product	Safety helmet