



PVC adhesive tape, Colour: YELLOW



Order data

| | |
|--------------|----------------|
| Order number | 083636 YELLOW |
| GTIN | 50021200456621 |
| Item class | 08M |

Description

Version:

The **3M™ 764i** can be used for non-critical application areas, such as colour marking and bundling. It is corrosion-resistant, flexible, supple, easy to apply and resistant to moisture. The 3M™ coloured marking and floor marking tapes are ideally suited for use in situations of building maintenance and for improving safety within the plant. The special structure of the coloured PVC adhesive tapes resists scratching, abrasion, weather and most chemicals. Easy to apply, very supple even on uneven surfaces.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Adhesive: Natural rubber

Colour: yellow

Length: 33 m

Width: 50 mm

Thickness: 0.125 mm

Technical description

| | |
|-----------|----------|
| Thickness | 0.125 mm |
|-----------|----------|

Data sheet

| | |
|----------------------------------------|---------------------|
| Manufacturer's designation | 764i |
| Width | 50 mm |
| Length | 33 m |
| Colour | yellow |
| Backing material | PVC film |
| Adhesive | Natural rubber |
| Storage temperature | 20 - 23 °C |
| Liner present | no |
| Stretch capability | 180 % |
| Special features | supple |
| Special features | moisture-resistant |
| Special features | corrosion-resistant |
| Special features | abrasion resistant |
| Type of adhesive tape | single-sided |
| temperature-resistant up to | 29 °C |
| Working life after date of manufacture | 12 mo |
| Tensile strength | 2.28 N/mm |
| Adhesive strength on steel | 0.21 N/mm |
| Application | Closing |
| Application | Marking |
| Application | Binding |
| Storage humidity | 50 - 60 % |
| Type of product | Adhesive tape |