

3M Scotch-Brite™

Bristle-Brush type C Ø 76 mm Shank Ø 6 mm, BB-ZS, Grit: 120**Order data**

Order number	573550 120
GTIN	54046719316361
Item class	53M

Description**Version:**

Cast special cleaning brushes are homogeneous grinding bodies with a mixture of precision-formed ceramic grit and Aluminium Oxide, and an **exceptionally long working life. Extremely flexible and versatile.**

The **radial** bristle brush consists of individual segments (approx. 1.6 mm wide).

Mandrel (**shank Ø 6 mm**) with cast segments.

With curved bristles (type C) for use on **profiled surfaces.**

Application:

Ensure the correct direction of rotation.

Requires no accessories for use on straight grinders or flexible shafts.

On virtually all materials, with the highest possible safety. Removal of rust, remains of adhesive, paint, light scratches and burrs. For smoothing, finishing, polishing, cleaning, and deburring.

Technical description

Grit	120
Colour	white

Brush $\varnothing D_1$	76 mm
maximum speed	10000 min ⁻¹
Brush width	10 mm
Shank $\varnothing D_s$	6 mm
Grinding medium code	Ceramic
Product name attribute	BB-ZS
Manufacturer's designation	BB-ZS
Type of product	Wheel brush