



## Digital external micrometer, Measuring range: 0-25mm



### Order data

Order number	421310 0-25
GTIN	4059192058388
Item class	43A

### Description

#### Version:

Innovative external micrometer with **10 mm tall characters** on sharp contrast display. Practical HOLD function for freezing the measured value for reliable, error-free reading. Measuring spindle hardened and ground. Carbide anvils. High performance ratchet with quick operation. Painted steel frame with thermal insulation. Button for changeover between relative and absolute measurement. Zero setting in any position.

#### Supplied with:

1 battery No. 081560 size CR2032, 1 setting standard from size 25-50.

Packaging: sturdy box

Calibration: B1

Scale divisions: 0.001 mm

Scale divisions: 0.00005 in

Error limit: 2  $\mu\text{m}$

Spindle  $\varnothing$ : 6.5 mm

Spindle pitch: 0.5 mm

### Technical description

Calibration	B1
Error limit	2 $\mu\text{m}$
Spindle $\varnothing$	6.5 mm
Scale divisions	0.00005 in
Spindle pitch	0.5 mm

Measuring range	0 - 25 mm
Scale divisions	0.001 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

## Services

Calibration External tube micrometer maximum measuring range 25 mm	012050 25
DAkkS calibration External micrometer maximum measuring range 100 mm	012060 100
Labelling laser-etched Type	018940
DAkkS calibration External micrometer maximum measuring range 100 mm	022010 100
Calibration External tube micrometer maximum measuring range 25 mm	022000 25

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------