



Digital external micrometer IP65, Measuring range: 25-50mm



Order data

Order number	421315 25-50
GTIN	4059192058401
Item class	43A

Description

Version:

Innovative external micrometer with **10 mm tall characters** on sharp contrast display. Practical HOLD function for freezing the measured value for reliable, error-free reading. Measuring spindle hardened and ground. Carbide anvils. High performance ratchet with quick operation. Painted steel frame with thermal insulation. Button for changeover between relative and absolute measurement. Zero setting in any position. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032, 1 setting standard from size 25-50.

Technical description

Scale divisions	0.00005 in
Error limit	2 μ m
Spindle \varnothing	6.5 mm
Calibration	B2
Scale divisions	0.001 mm
Measuring range	25 - 50 mm

Spindle pitch	0.5 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Micrometer setting standard overall length 25 mm	421100 25