



Digital external micrometer IP65, Measuring range: 75-100mm



Order data

Order number	421315 75-100
GTIN	4059192058425
Item class	43A

Description

Version:

Innovative external micrometer with **10 mm tall characters** on sharp contrast display. Practical HOLD function for freezing the measured value for reliable, error-free reading. Measuring spindle hardened and ground. Carbide anvils. High performance ratchet with quick operation. Painted steel frame with thermal insulation. Button for changeover between relative and absolute measurement. Zero setting in any position.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032, 1 setting standard from size 25-50.

Packaging: sturdy box

IP Index of Protection: IP 65

Calibration: B2

Scale divisions: 0.001 mm

Scale divisions: 0.00005 in

Error limit: 3 µm

Spindle Ø: 6.5 mm

Spindle pitch: 0.5 mm

Technical description

Calibration	B2
-------------	----

Spindle Ø	6.5 mm
Scale divisions	0.00005 in
Spindle pitch	0.5 mm
Measuring range	75 - 100 mm
Scale divisions	0.001 mm
Error limit	3 µm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Services

Labelling laser-etched Type	018940
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Micrometer setting standard overall length 100 mm	421100 100