

LESSMANN®
THE GERMAN BRUSH COMPANY**Cup brush Steel wire 0.35 mm, Brush Ø D1: 80mm****Order data**

Order number	573000 80
GTIN	4017359032404
Item class	57L

Description**Version:**

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines.

With **M14 internal thread**. With **M14 internal thread**.

Application:

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

Technical description

maximum speed	8500 min ⁻¹
Brush Ø D ₁	85 mm
Bristle thickness	0.35 mm
Length of brush section H ₁	25 mm
Thread M	M14
Brush material	Steel wire
Type of product	Cup brush

