

3M Scotch-Brite™

**Bristle-Brush type C Ø 76 mm Shank Ø 6 mm, BB-ZS, Grit: 220****Order data**

Order number	573550 220
GTIN	54046719316378
Item class	53M

**Description****Version:**

Cast special cleaning brushes are homogeneous grinding bodies with a mixture of precision-formed ceramic grit and Aluminium Oxide, and an **exceptionally long working life. Extremely flexible and versatile.**

The **radial** bristle brush consists of individual segments (approx. 1.6 mm wide).

Mandrel (**shank Ø 6 mm**) with cast segments.

With curved bristles (type C) for use on **profiled surfaces.**

**Application:**

Ensure the correct direction of rotation.

Requires no accessories for use on straight grinders or flexible shafts.

**On virtually all materials, with the highest possible safety.** Removal of rust, remains of adhesive, paint, light scratches and burrs. For smoothing, finishing, polishing, cleaning, and deburring.

**Technical description**

Grit	220
Brush Ø D <sub>1</sub>	76 mm

Colour	red
maximum speed	10000 min <sup>-1</sup>
Brush width	10 mm
Shank Ø D <sub>s</sub>	6 mm
Grinding medium code	Ceramic
Product name attribute	BB-ZS
Manufacturer's designation	BB-ZS
Type of product	Wheel brush