

**LESSMANN®**  
THE GERMAN BRUSH COMPANY**Wheel brush with shank Stainless steel wire 0.30 mm, Brush Ø D1× bristle width L1: 80X18mm****Order data**

Order number	574200 80X18
GTIN	4017359268469
Item class	57L

**Description****Version:**

Waved special high quality wire, **shank Ø 6 mm.**

**Application:**

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

**Technical description**

Bristle thickness	0.3 mm
Length of brush section H <sub>1</sub>	20 mm
Brush Ø D <sub>1</sub>	80 mm
maximum speed	15000 min <sup>-1</sup>
Brush width	18 mm
Bristle width L <sub>1</sub>	18 mm

Shank $\varnothing D_s$	6 mm
Brush material	Stainless steel wire
Twisted knotting	waved
Type of product	Wheel brush