

HOLEX

**Vanadium combination pliers, bright finished, with two-component grips,
Overall length: 160mm**



Order data

Order number	702995 160
GTIN	4045197887313
Item class	72B

Description

Version:

Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); suitable even for piano wire.

Jaws bright finished, handles with multi-component covering.

Standard:

DIN ISO 5746

Material:

Chrome vanadium steel, drop forged.

Technical description

Cutting capacity hard wire up to \varnothing	2 mm
Cutting capacity piano wire up to \varnothing	1.5 mm
overall length	160 mm
Standard	DIN ISO 5746
Jaw characteristics	inner face serrated
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC), pliers body drop forged

Material	Chrome vanadium steel.
Surface	bright finish
non-sparking	no
Type of product	Multi-function pliers