

3M Scotch-Brite™

**Bristle-Brush type C Ø 150 mm, BB-ZB, Grit: 80****Order data**

Order number	573555 80
GTIN	480113321542
Item class	53M

**Description****Version:**

Cast special cleaning brushes are homogeneous grinding bodies with a mixture of precision-formed ceramic grit and Aluminium Oxide, and an **exceptionally long working life. Extremely flexible and versatile.**

The **radial** bristle brush consists of individual segments (approx. 1.6 mm wide).

With curved bristles (type C) for use on **profiled surfaces.**

**Application:**

Ensure the correct direction of rotation.

**On virtually all materials, with the highest possible safety.** Removal of rust, remains of adhesive, paint, light scratches and burrs. For smoothing, finishing, polishing, cleaning, and deburring.

**Bore Ø 25.4 mm**, with reducer rings Ø 22.23 / 19 / 15.6 / 12.7 mm supplied. Extendable to any width with adaptor No. 573580. For use on double grinding machines or on straight grinders on flexible shafts with mandrel No. 556380 size 1.

**Technical description**

Colour	yellow
Brush Ø D <sub>1</sub>	150 mm

Grit	80
Brush width	12 mm
maximum speed	6000 min <sup>-1</sup>
Grinding medium code	Ceramic
Product name attribute	BB-ZB
Manufacturer's designation	BB-ZB
Type of product	Wheel brush

---

## Accessories

Mandrel Number of discs to be clamped 1-2	556380 1-2
Mandrel Number of discs to be clamped 1	556380 1
Extension adapter set, 4 pieces	573580