


Snipe nose pliers, angled, bright finished, with grips, Overall length: 160mm

Order data

Order number	713595 160
GTIN	4045197887405
Item class	72B

Description
Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws.

Jaws bright finished, handles with multi-component covering.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Jaw length	50 mm
overall length	160 mm
Jaw design	snipe nose, angled (40° – 45°)
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Handle	Multi-component covering
Material	Chrome vanadium steel, drop-forged and oil-hardened

Surface	bright finish
Type of product	Multi-function pliers