

HOLEX**Snipe-nose pliers, straight, bright finished, with grips, Overall length: 160mm**

Order data

Order number	713195 160
GTIN	4045197887382
Item class	72B

Description

Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws.

Jaws bright finished, handles with multi-component covering.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Jaw length	50 mm
Handle	Multi-component covering
overall length	160 mm
Jaw design	snipe nose, straight
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Material	Chromium vanadium steel
Surface	bright finish

Type of product

Multi-function pliers