



## Combination spanner, chrome-plated, Width across flats: 9 mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 613950 9      |
| GTIN         | 4045197159755 |
| Item class   | 62A           |

### Description

#### Version:

Drop-forged. With close tolerance jaw width.  
With oval shaft.

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 130 mm

maximum jaw height h<sub>1</sub>: 4.5 mm

maximum ring height h<sub>2 max</sub>: 8 mm

### Technical description

|  |             |
|--|-------------|
| maximum jaw height h <sub>1</sub>      | 4.5 mm      |
| Spanner length L                       | 130 mm      |
| Width across flats                     | 9 mm        |
| Width across flats                     | metric      |
| maximum ring height h <sub>2 max</sub> | 8 mm        |
| Standard                               | DIN 3113 A  |
| Standard                               | ISO 3318    |
| Standard                               | ISO 7738    |
| Ring setting                           | 15 °        |
| Manufacturing process                  | drop forged |

|                        |                       |
|------------------------|-----------------------|
| Material               | Chrome vanadium steel |
| Surface                | chrome plated         |
| Product name attribute | chrome-plated         |
| Type of product        | Spanner               |