



Carbide-tipped hammer drill "7X" SDS-plus, Øxoverall length: 5X110mm



Order data

Order number	789057 5X110
GTIN	3165140844147
Item class	76K

Description

Version:

4-cutter solid carbide head. Shaped cutters for high drilling performance, long working life and low wear. No digging in when drilling in reinforced concrete.

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. **2+2 flute** design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Shank: SDS Plus

Flute length: 50 mm

Technical description

Flute length	50 mm
Number of cutting edges Z	4
overall length	110 mm
Ø	5 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill