

HOLEX**Heavy-duty side cutter, bright finish, with grips, overall length: 160mm**

Order data

| | |
|--------------|---------------|
| Order number | 723395 160 |
| GTIN | 4045197887429 |
| Item class | 72B |

Description

Version:

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. High cutting performance due to optimum leverage.

Jaws bright finished, handles with multi-component covering.

Application:

For all types of wire (long working life even with hard wire). Heavy duty for the most demanding applications.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

| | |
|-------------------------------------|---------------------------|
| Cutting capacity soft wire up to Ø | 3.4 mm |
| Cutting capacity piano wire up to Ø | 2 mm |
| Cutting capacity hard wire up to Ø | 2.5 mm |
| overall length | 160 mm |
| Standard | DIN ISO 5749 |
| Handle | Multi-component covering |
| Manufacturing process | drop forged, oil-hardened |

| | |
|-----------------|-----------------------|
| Material | Chrome vanadium steel |
| Surface | bright finish |
| Type of product | Cutting pliers |