



Vanadium combination pliers VDE insulated, Overall length: 180mm



Order data

Order number	701852 180
GTIN	4045197887481
Item class	72B

Description

Version:

Chrome vanadium steel. Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); also suitable for piano wire. **For working at voltages up to 1000 V to DIN EN IEC 60900 / VDE 0682-201.**

Pliers bright finished, handles with multi-component covering.

Standard:

DIN ISO 5746

Technical description

Cutting capacity piano wire up to \varnothing	1.8 mm
overall length	180 mm
Cutting capacity hard wire up to \varnothing	2.2 mm
electrostatic characteristic	VDE 1000 V
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	similar to DIN ISO 5746
Jaw characteristics	serrated
Handle	Multi-component covering
Material	Chrome vanadium steel.
Surface	bright finish
non-sparking	no

Type of product

Multi-function pliers