



Vanadium combination pliers VDE insulated, Overall length: 180 mm



Order data

Order number	701852 180
GTIN	4045197887481
Item class	72B

Description

Version:

Chrome vanadium steel. Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); suitable even for piano wire. **Insulated to DIN EN 60900 / VDE 0682-201.**

Pliers bright finished, handles with multi-component covering.

Standard:

DIN ISO 5746

Cutting capacity hard wire up to \varnothing : 2.2 mm

Cutting capacity piano wire up to \varnothing : 1.8 mm

Technical description

Cutting capacity piano wire up to \varnothing	1.8 mm
overall length	180 mm
Cutting capacity hard wire up to \varnothing	2.2 mm
Standard	DIN EN 60900 / VDE 0682-201
Standard	similar to DIN ISO 5746
Handle	Multi-component covering
Material	Chrome vanadium steel.
Surface	bright finish
non-sparking	no
Type of product	Multi-function pliers

