



## Carbide-tipped hammer drill "7X" SDS-plus, Øxoverall length: 24X450mm



### Order data

Order number	789057 24X450
GTIN	3165140972635
Item class	76K

### Description

#### Version:

4-cutter solid carbide head. Shaped cutters for high drilling performance, long working life and low wear. No digging in when drilling in reinforced concrete.

#### Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. **2+2 flute** design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Shank: SDS Plus

Flute length: 400 mm

### Technical description

Number of cutting edges Z	4
Flute length	400 mm
Ø	24 mm
overall length	450 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill