



Vanadium combination pliers VDE insulated, Overall length: 200mm



Order data

Order number	701852 200
GTIN	4045197887498
Item class	72B

Description

Version:

Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); also suitable for piano wire. **For working at voltages up to 1000 V to DIN EN IEC 60900 / VDE 0682-201.** Pliers bright finished, handles with multi-component covering.

Standard:

DIN ISO 5746

Material:

Chrome vanadium steel, drop forged.

Technical description

overall length	200 mm
Cutting capacity hard wire up to Ø	2.5 mm
Cutting capacity piano wire up to Ø	2 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	similar to DIN ISO 5746
Jaw characteristics	serrated
Handle	Multi-component covering
Material	Chrome vanadium steel.
Surface	bright finish
non-sparking	no

Type of product

Multi-function pliers