

LESSMANN®
THE GERMAN BRUSH COMPANY
Cup brush Stainless steel wire 0.30 mm, Brush Ø D1: 60mm

Order data

Order number	573200 60
GTIN	4017359005781
Item class	57L

Description
Version:

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines.

With **M14 internal thread**. With **M14 internal thread**.

Application:

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

Technical description

Bristle thickness	0.3 mm
Brush Ø D ₁	65 mm
Length of brush section H ₁	20 mm
maximum speed	12000 min ⁻¹
Thread M	M14
Brush material	Stainless steel wire
Twisted knotting	waved

Type of product

Cup brush