



## Combination spanner, chrome-plated, Width across flats: 10 mm



### Order data

Order number	613950 10
GTIN	4045197159762
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw width.  
With oval shaft.

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 140 mm

maximum jaw height h<sub>1</sub>: 5 mm

maximum ring height h<sub>2 max</sub>: 9 mm

### Technical description

Width across flats	10 mm
Spanner length L	140 mm
maximum jaw height h <sub>1</sub>	5 mm
Width across flats	metric
maximum ring height h <sub>2 max</sub>	9 mm
Standard	DIN 3113 A
Standard	ISO 3318
Standard	ISO 7738
Ring setting	15 °
Manufacturing process	drop forged

Material	Chrome vanadium steel
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner