

LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush with shank Stainless steel wire 0.20 mm, Brush Ø D1× bristle width L1: 70X10mm****Order data**

| | |
|--------------|---------------|
| Order number | 574250 70X10 |
| GTIN | 4017359022740 |
| Item class | 57L |

Description**Version:**

Waved special high quality wire, **shank Ø 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

Technical description

| | |
|--|-------------------------|
| Length of brush section H ₁ | 19 mm |
| Brush Ø D ₁ | 70 mm |
| Bristle thickness | 0.2 mm |
| maximum speed | 15000 min ⁻¹ |
| Bristle width L ₁ | 10 mm |
| Shank Ø D _s | 6 mm |

| | |
|------------------|----------------------|
| Brush material | Stainless steel wire |
| Twisted knotting | waved |
| Type of product | Wheel brush |