

**Garant**
**Abrasive flap disc long life SiC, conical, Ø 125 mm, Grit: 40**

**Order data**

Order number	565381 40
GTIN	4045197887627
Item class	51M

**Description**
**Version:**

Particularly coarse **Silicon Carbide grit**, does not clog. Sturdy glass fibre pad for optimum contact pressure.

**Application:**

Edge and surface grinding of **aluminium and fibre-reinforced materials**.

maximum circumferential speed: 80 m/s

Shape description: dished

Bore Ø: 22.23 mm

**Technical description**

Shape description	dished
Grit	40
Disc Ø	125 mm
Bore Ø	22.23 mm
Grinding media	Silicon carbide (SiC)

Grinding medium code	SiC
Grinding media backing	Glass fibre pad
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
optimised for material	Aluminium
optimised for material	Fibre-reinforced plastics
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Carbide (HM)	suitable		
Ti	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
dry	suitable		