

LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush with shank Brass-coated steel wire 0.25 mm, Brush Ø D1× bristle width L1: 50X10mm****Order data**

Order number	574300 50X10
GTIN	4017359014622
Item class	57L

Description**Version:**

Waved special high quality wire, **shank Ø 6 mm.**
The high-tensile steel wire is coated with a thin layer of brass.

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.
For removal of rust and scale, and for cleaning

Technical description

Bristle thickness	0.25 mm
Brush Ø D ₁	50 mm
Length of brush section H ₁	12 mm
maximum speed	15000 min ⁻¹
Bristle width L ₁	10 mm

Shank $\varnothing D_s$	6 mm
Brush material	Steel wire, brass-coated
Twisted knotting	waved
Type of product	Wheel brush