



Snipe-nose pliers, straight VDE insulated, Overall length: 200mm



Order data

Order number	713351 200
GTIN	4045197888006
Item class	72B

Description

Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws.

Jaws bright finished, handles with multi-component covering.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	200 mm
Jaw length	73 mm
Handle	Multi-component covering
Jaw design	snipe nose, straight
Standard	similar to DIN ISO 5745
Standard	DIN EN IEC 60900 / VDE 0682-201
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened

Material	Chromium vanadium steel
Surface	bright finish
Type of product	Multi-function pliers