



## Snipe-nose pliers, straight VDE insulated, Overall length: 160 mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 713351 160    |
| GTIN         | 4045197887894 |
| Item class   | 72B           |

### Description

#### Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws. **Plastic-coated handles to DIN EN 60900 / VDE 0682-201 for working at voltages up to 1000 V.**

Jaws bright finished, handles with multi-component covering.

#### Standard:

**DIN ISO 5745**

#### Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Jaw length: 50 mm

### Technical description

|                     |   |
|---------------------|---|
| overall length      | 160 mm  |
| Handle              | Multi-component covering                          |
| Jaw length          | 50 mm   |
| Jaw design          | snipe nose, straight                              |
| Standard            | similar to DIN ISO 5745                           |
| Standard            | DIN EN 60900 / VDE 0682-201                       |
| Jaw characteristics | Cutting edges induction hardened (approx. 60 HRC) |
| Type of jaws        | inner face roughened                              |

|          |   |
|----------|---|
| Material | Chrome vanadium steel, drop-forged and oil-hardened |
| Surface  | bright finish                                       |