



## Snipe-nose pliers, straight VDE insulated, Overall length: 160mm



### Order data

Order number	713351 160
GTIN	4045197887894
Item class	72B

### Description

#### Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws.

Jaws bright finished, handles with multi-component covering.

**Insulated to DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V.

#### Standard:

**DIN ISO 5745**

#### Material:

Chrome vanadium steel, drop-forged and oil-hardened.

### Technical description

overall length	160 mm
Handle	Multi-component covering
Jaw length	50 mm
Jaw design	snipe nose, straight
Standard	similar to DIN ISO 5745
Standard	DIN EN IEC 60900 / VDE 0682-201
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened

Material	Chromium vanadium steel
Surface	bright finish
Type of product	Multi-function pliers