

**Heavy-duty side cutter VDE insulated, overall length: 180mm****Order data**

Order number	723551 180
GTIN	4045197888044
Item class	72B

Description**Version:**

Heavy-duty head, induction hardened cutting edges (approx. 64 HRC), laid-on joint with no play. Jaws bright finished, handles with multi-component covering.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened

Technical description

Cutting capacity piano wire up to \varnothing	2.2 mm
Cutting capacity hard wire up to \varnothing	2.7 mm
Cutting capacity soft wire up to \varnothing	3.8 mm
overall length	180 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel
Surface	bright finish

Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers