

**Heavy-duty side cutter VDE insulated, overall length: 160mm****Order data**

Order number	723551 160
GTIN	4045197888037
Item class	72B

**Description****Version:**

Heavy-duty head, induction hardened cutting edges (approx. 64 HRC), laid-on joint with no play. Jaws bright finished, handles with multi-component covering.

**Insulated to DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V.

**Standard:**

**DIN ISO 5749**

**Material:**

Chrome vanadium steel, drop-forged and oil-hardened

**Technical description**

overall length	160 mm
Cutting capacity soft wire up to Ø	3.4 mm
Cutting capacity hard wire up to Ø	2.5 mm
Cutting capacity piano wire up to Ø	2 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel
Surface	bright finish

Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers