



Heavy-duty side cutter VDE insulated, overall length: 200mm



Order data

Order number	723551 200
GTIN	4045197888051
Item class	72B

Description

Version:

Heavy-duty head, induction hardened cutting edges (approx. 64 HRC), laid-on joint with no play. Jaws bright finished, handles with multi-component covering.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened

Technical description

Cutting capacity soft wire up to Ø	4.2 mm
Cutting capacity hard wire up to Ø	3 mm
overall length	200 mm
Cutting capacity piano wire up to Ø	2.5 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel
Surface	bright finish

Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers