



Side cutter VDE insulated, overall length: 180mm



Order data

Order number	725351 180
GTIN	4045197888082
Item class	72B

Description

Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC).

Jaws bright finished, handles with multi-component covering.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged and oil-hardened.

Technical description

Cutting capacity soft wire up to \varnothing	4 mm
Cutting capacity hard wire up to \varnothing	2.5 mm
overall length	180 mm
Standard	DIN ISO 5749
Standard	DIN EN IEC 60900 / VDE 0682-201
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Special tool steel
Surface	bright finish

Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers