

**Garant****CaraFin diamond polishing block resilient, 98×69×22 mm, Grit: D64µm****Order data**

Order number	557510 D64
GTIN	4045197888372
Item class	51G

**Description****Version:**

**CaraFin diamond polishing tools** coated on one side with **mono-crystalline diamond**. The bonded diamond grit achieves significantly **higher effectiveness** than loose diamond grit in polishing pastes. Removal of grooves and oxide layers, polishing, smoothing.

**Advantage:**

Ancillary times for preparation and cleaning such as are required when polishing pastes are used are eliminated.

Of high-quality **resilient polyurethane foam**.

**Application:**

Ideally suited for fine polishing of **hard materials and non-ferrous metals**. Moulds optimally to the workpiece geometry.

Suitable for wet and dry polishing.

**Technical description**

Grinding medium code	D
Width	69 mm
Height	26 mm
Length	98 mm
Dimensions	98×69×22 mm
Polishing stage	Polishing

Series	CaraFin
Product name attribute	98×69×22 mm
Type of product	Polerblok

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		