

**LESSMANN®**  
THE GERMAN BRUSH COMPANY

## Wheel brush with shank Brass-coated steel wire 0.25 mm, Brush Ø D1× bristle width L1: 70X10mm



### Order data

Order number	574300 70X10
GTIN	4017359027974
Item class	57L

### Description

#### Version:

Waved special high quality wire, **shank Ø 6 mm.**

The high-tensile steel wire is coated with a thin layer of brass.

#### Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

### Technical description

Length of brush section H <sub>1</sub>	19 mm
Bristle thickness	0.25 mm
Brush Ø D <sub>1</sub>	70 mm
maximum speed	15000 min <sup>-1</sup>
Bristle width L <sub>1</sub>	9 mm
Shank Ø D <sub>s</sub>	6 mm

Brush material	Steel wire, brass-coated
Twisted knotting	waved
Type of product	Wheel brush