

LESSMANN®
THE GERMAN BRUSH COMPANY

Cup brush Right-left knotted, steel wire 0.50 mm, Brush Ø D1× thread M: 65XM14mm



Order data

Order number	572105 65XM14
GTIN	4017359380109
Item class	57L

Description

Version:

Smooth steel wire, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Right-left knotted for increased aggressiveness for heavy-duty brushing work. Very suitable for use at corners and edges, with a smooth action.

Application:

Specially to accept angle grinders.

With **M14 internal thread.**

Technical description

maximum speed	12500 min ⁻¹
Brush Ø D ₁	65 mm
Bristle thickness	0.5 mm
Safety support ring	no
Length of brush section H ₁	20 mm

Thread M	M14
Brush material	Steel wire
Twisted knotting	Right-left knotted
Type of product	Cup brush