

3M Scotch-Brite™

**Bristle-Brush type C Ø 25 mm Set 24 pieces, shank Ø 3 mm., RB-ZB, Grit: 120****Order data**

Order number	573545 120
GTIN	30048011276138
Item class	53M

**Description****Version:**

Cast special cleaning brushes are homogeneous grinding bodies with a mixture of precision-formed ceramic grit and Aluminium Oxide, and an **exceptionally long working life. Extremely flexible and versatile.**

The **radial** bristle brush consists of individual segments (approx. 1.6 mm wide).

Removable mandrel (**shank Ø 3 mm**). Segments can be combined to make up any desired brush width.

With curved bristles (type C) for use on **profiled surfaces.**

**Application:**

Ensure the correct direction of rotation.

Requires no accessories for use on straight grinders or flexible shafts.

**On virtually all materials, with the highest possible safety.** Removal of rust, remains of adhesive, paint, light scratches and burrs. For smoothing, finishing, polishing, cleaning, and deburring.

**Supplied with:**

24 individual segments (approx. 1.6 mm wide) **including mandrel** with shank Ø 3 mm.

**Technical description**

Grit	120
Colour	white
Brush $\varnothing D_1$	25 mm
maximum speed	35000 min <sup>-1</sup>
Brush width	1.6 - 10 mm
Shank $\varnothing D_s$	3 mm
Grinding medium code	Ceramic
Product name attribute	RB-ZB
Manufacturer's designation	RB-ZB
Type of product	Wheel brush