

LESSMANN[®]
THE GERMAN BRUSH COMPANY**Tube brush micro-abrasive (A) 600 grit, Brush Ø D1: 4,8mm****Order data**

Order number	574470 4,8
GTIN	4017359171301
Item class	57L

Description**Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles.

Fine aluminium oxide bristles (A) in **600 grit**, bristle Ø **0.30 mm**, overall length 125 mm, brush section length 25 mm.

Application:

Abrasive nylon brushes work at both the tips and the sides of the bristles. The continued exposure of new abrasive material ensures an **even abrasive effect**. For **deburring** (cross) bores, O-ring recesses, and for **cleaning** and **polishing** nozzles and small hydraulic bores.

Technical description

Brush Ø D ₁	4.8 mm
Working length L ₃	25 mm
Shank Ø D _s	2.2 mm
Type of product	Tube brush