


**LESSMANN®**  
THE GERMAN BRUSH COMPANY**Wheel brush with shank Steel wire 0.20 mm, Brush Ø D1× bristle width L1:  
40X10mm****Order data**

Order number	574100 40X10
GTIN	4017359007082
Item class	57L

**Description****Version:**

Waved special high quality wire, **shank Ø 6 mm.**

**Application:**

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

**Technical description**

Length of brush section H <sub>1</sub>	9 mm
Brush Ø D <sub>1</sub>	40 mm
Bristle thickness	0.2 mm
maximum speed	18000 min <sup>-1</sup>
Bristle width L <sub>1</sub>	10 mm
Shank Ø D <sub>s</sub>	6 mm

Brush material	Steel wire
Twisted knotting	waved
Type of product	Wheel brush