

LESSMANN[®]
THE GERMAN BRUSH COMPANY**Tube brush micro-abrasive (SiC) 120 grit, Brush Ø D1: 25mm****Order data**

Order number	574475 25
GTIN	4017359195109
Item class	57L

Description**Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles.

Strong silicon carbide bristles (SiC) in **120 grit and 320 grit**, bristle Ø **0.60mm**, overall length 125mm.

Application:

Abrasive nylon brushes work at both the tips and the sides of the bristles. The continued exposure of new abrasive material ensures an **even abrasive effect**. For **deburring** (cross) bores, O-ring recesses, and for **cleaning** and **polishing** nozzles and small hydraulic bores.

Technical description

Brush Ø D ₁	25 mm
Working length L ₃	65 mm
Shank Ø D _s	5.7 mm
Type of product	Tube brush